

Silicone sheet

**Dimension**

200 x 200 mm

300 x 300 mm

425 x 425 mm

Thickness

0,25 mm*

0,50 mm*

1,00 mm*

1,25 mm

1,50 mm*

1,0 – 30,0 mm

Thickness tolerances:

+/- 0,05 mm

+/- 0,1 mm

M2 DIN ISO 3302-1

or min. +/- 0,2 mm up to 5 mm thickness,

min. +/- 0,3 mm from 5 mm thickness

Quality:**Hardness:**

from 20° up to 80° Shore A DIN 53505,
depending on thickness

***on stock**

Silikon, 60 +/- 5° Shore, translucent
platinum-catalysed

Colours:

translucent or other colours on arrangement

Conformity:

according to recommendations/ regulations:

- BfR XV.Silicone
- FDA § 177.2600

Temperature resistance:

from -60° up to +250° C,
special qualities up to +300° C

on request:

- USP Class VI
- ISO 10993

Issue 09/2023

This document is not subject to updates.