

# Datasheet

# SOLIMIDE® AC-530



SOLIMIDE® AC-530 polyimide foam is utilized in aircraft, aerospace and industrial markets as a lightweight, non-wicking, thermal and acoustic insulation material where low fire, toxicity and smoke generation are critical. It is formaldehyde-free and demonstrates excellent long term stability under humid conditions and after temperature cycling. SOLIMIDE® AC-530 insulation is used in a variety of applications, including aircraft fuselage, under floor, ECS ducts and equipment, as well as expansion and contraction joints in cryogenic environments. The foam can be cut into numerous shapes and sizes, and is compatible with many different facings, coatings and adhesives to meet end-use requirements.

## Specifications/ Certificates

- Boeing BMS 8-300
- Airbus AIMS 04-14-004
- Boeing (Douglas) DMS 2330
- ASTM C 1482
- KBR TS (Pipe Supports, Components and Fabricated Assemblies)
- SOLIMIDE® Foams may meet additional specifications that are not listed here. Please contact us to determine if it meets your specifications or other requirements.



Properties	Units	Values	Testing
Typical Density*	kg/m <sup>3</sup> (lb/ft <sup>3</sup> )	5.4 (0.34)	ASTM D3574 Test A, ISO 845
FAA Radiant Panel FAR 25.856(a)		Pass	
Smoke Developed Index Flaming and Non-Flaming Modes		< 5	ASTM E662
Noise Reduction Coefficient (NRC), 25mm (1in)		0.7	ASTM C423 and E795, Mounting A
Max Continuous Use Temperature	°C (°F)	200 (400)	
Thermal Conductivity at 24°C (75°F)	W/mK (BTU-in/hr-ft <sup>2</sup> -°F)	≤ 0.050 (0.35)	ASTM C518
Offgassing / Outgassing TMI	%	< 1.0	ASTM E595
Offgassing / Outgassing CVCM	%	< 0.1	ASTM E595

\*Subject to normal manufacturing variation

The information included in this data sheet is believed to be accurate and reliable. Boyd assumes no responsibility for end use applications and no performance warranty is express or implied.